## **Fact Sheet**





Seal inspection by vision: With SealSecure you meet key criteria for an optimal product quality – a clean and undamaged seal. The system checks packages for any damaged seals. Packages which do not meet the defined criteria are automatically rejected.




More information High performance with a wide range of solutions and options.

Specifications	Facts	Details
Functions	Detects	
	<ul> <li>Contaminations/foreign bodies in the seal on trays, flow packs and cups</li> </ul>	Contaminations/foreign bodies from 1 mm²
	<ul> <li>No integrated rejection device but reporting of detected errors</li> </ul>	Transmits information in two ways:
		<ul> <li>TCP/IP protocol: Sends the position information of the individual packages within the group</li> </ul>
		<ul> <li>Sends digital signals to peripheral devices (printer, robot, rejector) with package tracking up to the thermoformer output</li> </ul>
Integration	All parameters are checked by the sensors integrated in the thermoformer.	
	SealSecure T is compatible with all common thermoformers and can be used for numerous inspection tasks	
Versions	basic	Recognizes contaminations in the seal
Camera system	One sensor	Sensor consists of camera, lighting, and accessories.
		The image recording field adjusts to the size of the products to be inspected. Life of LED lighting is more than 5 years.
	Line scan camera	The pixel size (0.10 to 0.16 mm²) allows detection as from one square millimeter.
	Protected against ambient light and manipulations	No external influences on the inspection results
Dimensions	Sensor: 460-870 mm x 388 mm x 310 mm (L x W x H)	The length of the sensor housing depends on the film width (340 to 750 mm). Other lengths on request.
	Back lighting: 460-870 mm x 238 mm x 190 mm (L x W x H)	The length of the housing depends on the film width (340 to 750 mm). Other lengths on request.
	Control cabinet on castors: 650 mm (850 mm with cooling device) x 780 mm x 1,800 mm (2,130 mm with signal lamp) (L x W x H)	Color touch screen, processing system, operating elements for the lighting, power supplies, input/output terminal blocks and connector housing
	Coating to protect supply, control and com- munication cables between sensors, lighting and control cabinet	
IP rating	IP66 for sensors and lighting	All optical inspection components are integrated in a tightly sealed stainless steel housing
	IP65 for the control cabinet	

Device performance	15 operating cycles per minute	Adjustable to common maximum conveyor speeds
Processing system	Industrial PC	- Operating system: Windows IoT Standard 10
		<ul> <li>Processor Intel® Core™ i7</li> </ul>
		<ul> <li>Real time image processing card</li> </ul>
Interfaces	USB	
	ETHERNET	Connection to customer network via Ethernet (TCP/IP possible)
Compatibility	Hardware integration in the thermoformer	
	Compatible with most installed thermoformers or project planning in cooperation with thermoformer manufacturer	
	Protocol of communication with the peripheral devices	
	Printing systems, external rejection systems (retraction belt, divider, robot etc.)	
Power supply	230 VAC; 50 Hz / 110 VAC, 60 Hz (incl. transformer) + single phase + ground uninterruptable power supply (UPS) system for computing and display units	Open to other local voltage with a transformer
Ambient temperature	1 °C to 35 °C	With cooling device as from 10 °C
Humidity	Max. 85%, non-condensing	
Optical signaling device	Signal lamp	Visual alarm for detection of non-conforming package
By-pass mode	Inspection tasks can be deactivated	
Specifications	Facts	Details
Checks	Checking of product presence in a package	Other inspections based on feasibility upon request
	Appearance and arrangement of the products in the packaging	
Production control	Communication interface to the process	Data transfer within the factory concerning:
		<ul> <li>System performance (monitoring of the device cycle, process data etc.)</li> </ul>
		<ul> <li>Production monitoring (history of batch changes, test statistics, archiving of batch changes)</li> </ul>
IP rating	IP66 for the control cabinet	- Buttons
		<ul> <li>Emergency stop switch</li> </ul>
		– Display
US-Special current transformer	115 V AC	

HF\_SealSecure T\_V1\_EN Subject to technical modifications Page 2 / 3

## **Dimensional drawings**



## Bizerba SE & Co. KG

Wilhelm-Kraut-Straße 65 72336 Balingen

T +49 7433 12-0 fax: +49 7433 12-2696 marketing@bizerba.com

www.bizerba.com

HF\_SealSecure T\_V1\_EN Subject to technical modifications Page 3 / 3